



CLIFE-PRO-SM-WL-D2

Lifelight Pro Emergency, Surface Mount, LP, DALI-2
Emergency, Warehouse Lens



PRODUCT INFORMATION

Part Number	CLIFE-PRO-SM-WL-D2
MIC	AUT00000006501
Description	Lifelight Pro Emergency, Surface Mount, LP, DALI-2 Emergency, Warehouse Lens
Construction	Polycarbonate Enclosure
Mounting	Surface Mounted
Dimensions L x W x H	247mm x 129mm x 51mm
Weight	0.8kg
Operating Mode	Non-maintained
Testing System	DALI-2
Battery	Lithium Iron Phosphate, 3.2V 6400mAh
Charging Method	Intelligent Current Limited Constant Voltage
Lamp(s)	Dual LED (Lifetime warranty on the lamp head and loom assembly)
Operating Voltage	240V AC; 50Hz
Power Consumption	0.7W (Standby) 3.0W (Max)
IP Rating	IP20
IK Rating	IK08
Operating Temperature	0°C to 40°C
AS2293 Classification	C0 = D63, C90 = D25
Applicable Standards	AS/NZS3820, CISPR15, AS/NZS2293.3
Compliance Marking (RCM)	

REPLACEMENT PARTS

PART NUMBER	DESCRIPTION
1550231	Battery
1160326	Warehouse Lens
8050880	LED Assembly
8003501	Emergency Driver
8003062	DALI-2 Node

The product details described in this document are current as at the version date of the document. We reserve the right to change product design, specifications or materials (Specifications) as part of our continuous improvement program. Please confirm the applicable Specifications at the time of placing your order



CLIFE-PRO-SM-WL-D2

Lifelight Pro Emergency, Surface Mount, LP, DALI-2
Emergency, Warehouse Lens

SPACING TABLE

Manufacturer recommended spacing table and mounting heights for $\leq 3.6\text{m}$ aisle width, based on direct illuminance calculations (AS/NZS 2293.1); minimum light level of 0.2lx / 0.5lx avg									
Mounting Height [m]	6.0	7.0	8.0	9.0	10.0	11.0	12.0	13.0	14.0
Fitting to Wall [m]	23.2	25.2	27.5	30.2	32.0	33.6	34.6	35.6	38.6
Fitting to Fitting [m]	55.0	61.1	66.8	72.1	74.2	58.6	45.0	33.5	18.3

Note: These spacing tables are a guide to assist with placement of the emergency luminaire and any design must be verified via illuminance calculations in accordance with AS/NZS2293.1:2018, section 4.6.1.3 *Illuminance calculations*

ISOLUX PATTERN

