LIFELIGHT CORRIDOR LENS

MANUFACTURER RECOMMENDED SPACING TABLE (Minimum Light Level of 0.2 Lux) For up to 2.5m corridor aisle width at various mounting heights to comply with 0.2lx min / 0.5lx avg AS/NZS 2293.1 requirements													
Mounting Height (m)		2.4m	2.7m	3.0m	3.3m	3.6m	4.0m	4.5m	5.0m	6.0m	7.0m		
NUMBER OF FITTINGS													
Single Fitting - Max Aisle Length (m)		23.4	25.4	28.4	30.0	32.4	34.2	36.8	39.4	44.0	19.2		
Two Fittings - Max Aisle Length (m)		54.9	59.4	64.9	68.7	73.3	77.8	83.6	89.3	99.4	69.2		
SPACINGS													
Fitting to Wall (m)		11.7	12.7	14.2	15.0	16.2	17.1	18.4	19.7	22.0	9.6		
Fitting to Fitting (m)		31.4	34.0	36.4	38.7	40.8	43.6	46.8	49.8	55.3	49.9		

 $Manufacturer's \ recommended \ spacing \ tables \ are \ a \ guide \ only \ and \ use \ of \ these \ product \ must \ be \ supported \ with \ illuminance \ calculations \ by the "designer" for the \ specific \ building/application \ in \ accordance \ with \ AS/NZS2293.1.$

Please contact Clevertronics for spacing tables on alternative aisle widths or design support if required. IES files available on request.

LIFELIGHT SURFACE MOUNT WAREHOUSE LENS

MANUFACTURER RECOMMENDED SPACING TABLE (Minimum Light Level of 0.2 Lux) For up to 3.6m racking aisle width at various mounting heights to comply with 1.0lx min AS/NZS 2293.1 requirements																		
Mounting Height (m)		2.4m	2.7m	3.0m	3.3m	3.6m	4.0m	4.5m	5.0m	6.0m	7.0m	8.0m	9.0m	10.0m	11.0m	12.0m	13.0m	14.0m
NUMBER OF FITTINGS																		
Single Fitting - Max A	Aisle Length (m)	23.0	25.5	27.5	29.5	31.5	34.1	37.1	40.1	46.1	51.1	56.0	60.2	63.5	54.5	28.4	n/a	n/a
Two Fittings - Max Aisle Length (m)		52.0	57.1	61.5	65.8	70.1	75.6	82.1	88.5	101.0	112.0	122.7	132.2	138.8	112.9	74.0	105.5	97.2
SPACINGS																		
Fitting to Wall (m)	2	11.4	12.7	13.7	14.7	15.7	17.0	18.5	20.0	23.0	25.5	28.0	30.1	31.7	27.2	14.2	35.8	39.3
Fitting to Fitting (m)		29.2	31.7	34.1	36.4	38.7	41.6	45.1	48.5	55.0	61.0	66.7	72.0	75.4	58.5	45.6	33.9	18.6

 $Manufacturer's \ recommended \ spacing \ tables \ are \ a \ guide \ only \ and \ use \ of \ these \ product \ must \ be \ supported \ with \ illuminance \ calculations \ by the "designer" for the \ specific \ building/application \ in \ accordance \ with \ AS/NZS2293.1.$

Please contact Clevertronics for spacing tables on alternative aisle widths or design support if required. IES files available on request. *Warranty information located at: https://clevertronics.com.au/warranty-statement/



^{*}Warranty information located at: https://clevertronics.com.au/warranty-statement/

EMERGENCY LUMINAIRES MAXIMUM SPACING AND MOUNTING HEIGHTS (BASED ON 1 LX)

LIFELIGHT CORRIDOR LENS

MANUFACTURER RECOMMENDED SPACING TABLE (Minimum Light Level of 1.0 Lux) For up to 2.5m corridor width at various mounting heights to comply with 1.0lx min AS/NZS2293.1 requirements													
Mounting Height (m)		2.4m	2.7m	3.0m	3.3m	3.6m	4.0m	4.5m	5.0m	6.0m	7.0m		
NUMBER OF FITTINGS													
Single Fitting - Max Aisle Length (m)		8.5	10.5	11.4	12.5	12.5	11.5	9.6	8.6	3.5	n/a		
Two Fittings - Max Aisle Length (m)		26.0	30.1	32.9	35.0	36.0	35.9	34.0	33.2	21.9	n/a		
SPACINGS													
Fitting to Wall (m)	•	4.2	5.2	5.7	6.2	6.2	5.7	4.8	4.3	1.7	n/a		
Fitting to Fitting (m)	•••	17.5	19.6	21.4	22.5	23.5	24.4	24.4	24.6	18.4	n/a		

Manufacturer's recommended spacing tables are a guide only and use of these product must be supported with illuminance calculations by the "designer" for the specific building/application in accordance with AS/NZS2293.1.

Please contact Clevertronics for spacing tables on alternative aisle widths or design support if required. IES files available on request. *Warranty information located at: https://clevertronics.com.au/warranty-statement/

LIFELIGHT SURFACE MOUNT WAREHOUSE LENS

MANUFACTURER RECOMMENDED SPACING TABLE (Minimum Light Level of 1.0 Lux) For up to 2.5m racking aisle width at various mounting heights to comply with 1.0lx min AS/NZS2293.1 requirements																
Mounting Height (m)		2.4m	2.7m	3.0m	3.3m	3.6m	4.0m	4.5m	5.0m	6.0m	7.0m	8.0m	9.0m	10.0m	11.0m	12.0m
NUMBER OF FITTINGS																
Single Fitting - Max A	Aisle Length (m)	17.4	18.4	20.4	22.4	23.4	25.4	27.4	26.4	28.4	18.4	16.6	n/a	n/a	n/a	n/a
Two Fittings - Max Ai	sle Length (m)	38.5	41.6	45.4	49.2	51.8	55.9	60.3	61.4	66.1	56.5	54.0	34.4	n/a	n/a	n/a
SPACINGS																
Fitting to Wall (m)	•	8.7	9.2	10.2	11.2	11.7	12.7	13.7	13.2	14.2	9.2	8.3	n/a	n/a	n/a	n/a
Fitting to Fitting (m)		21.1	23.1	25.0	26.7	28.3	30.4	32.8	34.9	37.6	37.9	37.4	34.4	27.5	16.2	12.1

 $Manufacturer's \ recommended \ spacing \ tables \ are \ a \ guide \ only \ and \ use \ of \ these \ product \ must \ be \ supported \ with \ illuminance \ calculations \ by the "designer" for the \ specific \ building/application \ in \ accordance \ with \ AS/NZS2293.1.$

 $Please \ contact \ Clever tronics for spacing \ tables on \ alternative \ aisle \ widths \ or \ design \ support \ if \ required. \ IES \ files \ available \ on \ request.$ $*Warranty information \ located \ at: \ https://clevertronics.com.au/warranty-statement/$

LIFELIGHT SURFACE MOUNT WAREHOUSE LENS

MANUFACTURER RECOMMENDED SPACING TABLE (Minimum Light Level of 1.0 Lux) For up to 3.6m racking aisle width at various mounting heights to comply with 1.0lx min AS/NZS2293.1 requirements																
Mounting Height (m)		2.4m	2.7m	3.0m	3.3m	3.6m	4.0m	4.5m	5.0m	6.0m	7.0m	8.0m	9.0m	10.0m	11.0m	12.0m
NUMBER OF FITTINGS																
Single Fitting - Max Aisle Length (m)		8.40	9.40	9.40	20.40	21.40	23.40	25.40	26.40	28.40	17.40	9.60	0.00	n/a	n/a	n/a
Two Fittings - Max Ais	Two Fittings - Max Aisle Length (m)		28.90	11.75	45.90	48.70	52.90	57.40	60.40	65.30	54.00	46.30	n/a	n/a	n/a	n/a
SPACINGS																
Fitting to Wall (m)	•	4.20	4.70	4.70	10.20	10.70	11.70	12.70	13.20	14.20	8.70	4.80	0.00	n/a	n/a	n/a
Fitting to Fitting (m)		17.30	19.50	2.35	25.50	27.30	29.50	32.00	34.00	36.90	36.60	36.70	34.10	27.50	15.9	n/a

Manufacturer's recommended spacing tables are a guide only and use of these product must be supported with illuminance calculations by the "designer" for the specific building/application in accordance with AS/NZS2293.1.

Please contact Clevertronics for spacing tables on alternative aisle widths or design support if required. IES files available on request. *Warranty information located at: https://clevertronics.com.au/warranty-statement/

clevertronics.co.nz clevertronics.com.au

